

Selective Laser Sintering Printers

Production thermoplastic parts with SLS 3D printers



3D Systems' Selective Laser Sintering (SLS) 3D printers produce tough, functional complex parts, with excellent surface finish, resolution, accuracy, repeatability and low total cost of operations.

Limitless possibilities with tool-less manufacturing

The ultimate 3D printing technology for thermoplastic parts, without compromise

ELIMINATE THE TIME AND EXPENSE OF TOOLING

Direct 3D production from a CAD file eliminates the cost and time involved in tooling and fixtures.

STREAMLINE YOUR WORKFLOW

Eliminate extensive programming and fixturing to free up your machinists. Drastically reduce assembly times by reducing total part count.

INCREASE MANUFACTURING AGILITY

Additive manufacturing requires no tooling, reducing overhead and increasing economies of scope.

DESIGN FOR FUNCTION

SLS technology frees designers from the restrictions of traditional manufacturing. Complete assemblies can be printed as one part, improving functionality, reducing cost and increasing reliability.

SLS 380 Printer

Repeatable parts at high yield for scalable batch manufacturing

High performance SLS 3D printer featuring real-time thermal management and control, delivering high part repeatability and throughput, together with reduced operating costs for more effective and efficient production manufacturing runs.

CLOSED LOOP THERMAL MANAGEMENT

Closed-loop process controls consistently produce accurate parts across multiple builds, machines and sites. In addition to a new water-cooled laser, the system uses a unique algorithm, eight separately calibrated heaters, together with an integrated high-resolution IR camera to manage, monitor and control in real-time the thermal uniformity within the build chamber for every sintered build-layer and for the duration of the part build process.

DELIVER MORE CONSISTENT SLS BATCH PARTS

With consistent thermal uniformity across the build process, you can deliver parts with improved dimensional and mechanical performance and deliver batch jobs with higher yields at lower operating costs.

sPro™ 140 & 230 SLS Printers

Low cost of ownership with high throughput and large capacity for end-use parts

Ideal for volume production of 3D printed small to medium sized parts, as well as the production of large parts in one single piece for increased part strength and reduced assembly time.

HIGH CAPACITY MANUFACTURING - Address your high-volume needs with fast production, high-density build volume capacity, or build large parts up to 750 mm/30 in long with the sPro 230 printer.

LOW COST OF OWNERSHIP - Offering high throughput and large capacity, the sPro 140 and sPro 230 produce high quality, robust nylon or composite parts with lower cost of ownership.



SLS Material Delivery Options

Customize material handling solutions to optimize operational efficiency

SLS MATERIAL DELIVERY MODULE

Enables the use of multiple materials on a single printer. Quickly change materials with minimum labor to expand application offerings.

MQC 600 SINGLE

Connects to one SLS printer and fully automates material feeding and an integrated breakout station for post-processing.

MQC 600 FLEX

Optimized to deliver material to up to four printers simultaneously, minimizes waste, and eliminates operator intervention. Features fully-automated material feeding and an integrated breakout station for post-processing.



Robust Thermoplastics for a Variety of Applications

Produce tough, durable parts from the wide DuraForm® materials portfolio that has been optimized, validated and tested to ensure quality, with uniform 3D mechanical properties. When you compare material properties, you'll find DuraForm SLS materials compare very well with common injection molding materials. These materials are ideal for both production and prototype parts.

NYLON/POLYAMIDE 12 THERMOPLASTICS

Extra strong thermoplastics with superior mechanical properties, surface quality and fine-feature resolution for end-use parts that stand up to the rigors of long-term real world use, replacing traditionally injection molded articles. Food-grade, medical grade, flame-retardant capable.

HIGH ELONGATION NYLON COPOLYMER

A novel, nylon copolymer that features high impact resistance with high elongation at break in any direction, including Z. Engineered for easy processing and high recyclability, this production grade material is ideal for end-use parts or prototypes requiring long-term use and stability.

FILLED NYLON/POLYAMIDE THERMOPLASTICS

For even greater engineered end-use part performance, 3D Systems has developed DuraForm SLS materials with fillers such as glass, aluminum and mineral fiber. These materials offer a choice of advanced properties in terms of stiffness, temperature resistance, strength and surface finish.

NYLON/POLYAMIDE 11 THERMOPLASTICS

Tough, impact and fatigue-resistant Nylon 11 materials for prototypes and end-use parts requiring molded-part performance in harsh environments. Ideal for snap-fit and living hinges—plastic parts that are flexible and bounce back to their original shape.

Note: availability varies by printer model. Please check our SLS materials selection guide for compatibility



HOUSINGS

Manufacture in small to medium lot sizes, and bridge the time until final tools are manufactured.



JIGS AND FIXTURES

Print complex assembly aids and free up CNC time for other projects.



MACHINERY COMPONENTS

Integrate functionality and replace complex assemblies.



MEDICAL DEVICES

Production of patient-specific medical devices



FUNCTIONAL TESTING

Test your prototypes for functionality—such as heat run cycle tests



CONSUMER GOODS

High-speed production for small lots and custom products.



DUCTING

Optimize flow and fit in tight spaces with the freedom to print duct-work that is impossible to mold.

Sp 3D Sprint®

All-in-one software for plastic printing

An exclusive software for 3D Systems plastic printers to prepare and optimize CAD data, and manage the SLS printing process. Tools for high-performance—such as high-density automatic 3D nesting, quality checks for pre-build verification, repair options, print queue tool for efficient build planning, cage structure generator for small parts enclosure, and more features—bring increased productivity and quality to your SLS production process without needing additional third party software.



Selective Laser Sintering Printers

Production thermoplastic parts with SLS 3D printers

	SLS 380	sPro™ 140	sPro™ 230
PRINTER PROPERTIES			
3D Printer Size Crated (WxDxH)	204 x 153 x 258 cm (80 x 60 x 101 in)	229 x 178 x 257 cm (90 x 70 x 101 in)	267 x 224 x 292 cm (105 x 88 x 115 in)
3D Printer Size Uncrated (WxDxH)	174 x 123 x 230 cm (69 x 48 x 90 in)	213 x 163 x 241 cm (84 x 64 x 95 in)	251 x 208 x 274 cm (99 x 82 x 108 in)
3D Printer Weight Crated 3D Printer Weight Uncrated (Weights do not incl. MQC, MDM or BOS)	1485 kg (3274 lb) 1360 kg (3000 lb)	2250 kg (4950 lbs) 2224 kg (4893 lbs)	2539 kg (5586 lbs) 2541 kg (5531 lbs)
Electrical Requirements			
System	208 VAC/10 kVA, 50/60 Hz, 3 PH	208 VAC/17 kVA, 50/60Hz, 3 PH	208 VAC/17 kVA, 50/60Hz, 3 PH
MQC Single or Flex	208-230VAC, 50/60Hz, 1PH		
MDM			
Laser Power Type	100 W / CO ₂	70 W / CO ₂	70 W / CO ₂
Powder Recycling and Handling	Automatic (Material Quality Control system servicing up to four printers simultaneously)	Automatic (Integrated Recycling System servicing up to three printers simultaneously)	Automatic (Integrated Recycling System servicing up to three printers simultaneously)
Systems Warranty	One-year warranty, under 3D Systems purchase terms and conditions		

PRINTING SPECIFICATIONS			
Max Build Envelope Capacity (xyz)¹	381 x 330 x 460 mm (15 x 13 x 18 in) 57.5 l (3510 cu in)	550 x 550 x 460 mm (22 x 22 x 18 in) 139 l (8500 cu in)	550 x 550 x 750 mm (22 x 22 x 30 in) 227 l (13900 cu in)
Layer Thickness Range (typical)	0.08 – 0.15 mm 0.003 – 0.006 in (0.10 mm, 0.004 in)	0.08 – 0.15 mm 0.003 – 0.006 in (0.10 mm, 0.004 in)	0.08 – 0.15 mm 0.003 – 0.006 in (0.10 mm, 0.004 in)
Volume Build Rate	2.7 l/hr	3.0 l/hr	3.0 l/hr
Imaging System	ProScan™ DX Digital High Speed	ProScan™ Standard Digital Imaging Systems	ProScan™ Standard Digital Imaging Systems
Scanning Speed			
Fill	12.7 m/s (500 in/s)	10 m/s (400 in/s)	10 m/s (400 in/s)
Outline	5 m/s (200 in/s)	5 m/s (200 in/s)	5 m/s (200 in/s)
Powder Layout	Variable Speed Counter Rotating Roller	Counter Rotating Roller	Counter Rotating Roller
Thermal control	Consistent part quality build to build with eight zone heater control with thermal imaging camera closed loop feedback.		

MATERIALS	
Build Materials	See material selector guide and individual material datasheets for specifications on available materials.

SOFTWARE AND NETWORK	
Included Software	3D Sprint®
3D Sprint® Software	Prepares and optimizes design file data, and manages the additive manufacturing process on plastic 3D printers.
3D Connect™ Capable	3D Connect™ Service provides a secure cloud-based connection to 3D Systems service teams for support.

¹ Maximum part size is dependent on geometry, among other factors.

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, material combined with, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2022 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo, DuraForm, and 3D Sprint are registered trademarks and 3D Connect and sPro are trademarks of 3D Systems, Inc.